



CERT

DVGW type examination certificate

DVGW-Baumusterprüfzertifikat

DW-6201CL0241

Registration Number
Registriernummer

Field of Application
Anwendungsbereich

products of water supply
Produkte der Wasserversorgung

Owner of Certificate
Zertifikatinhaber

GEMÜ Gebr. Müller Apparatebau GmbH & Co. KG
Fritz-Müller-Straße 6-8, D-74653 Ingelfingen-Criesbach

Distributor
Vertreiber

GEMÜ Gebr. Müller Apparatebau GmbH & Co. KG
Fritz-Müller-Straße 6-8, D-74653 Ingelfingen-Criesbach

Product Category
Produktart

Valves for water supply: Butterfly valve (6201)

Product description
Produktbezeichnung

centric butterfly valve (Wafer, Lug respectively U-form) for the drinking water supply

Model
Modell

VICTORIA

Test reports
Prüfberichte

Type testing: 2-0076/22 T01 from 13.01.2023 (TZW)
Laboratory control test: 2-0007/21 from 02.09.2021 (TZW)
Laboratory control test: A0 007/17 from 13.04.2017 (TZW)
Type testing: A0 001/09 + A0 002/09 from 20.06.2010 (TZW)
Hygiene: 2200455 / 17319 / 1H from 09.09.2022 (ÖFI)

Test basis
Prüfgrundlagen

DVGW W 363-(P) (01.06.2010)
DIN EN 1074-1 (01.07.2000)
DIN EN 1074-2 (01.07.2004)
UBA BWGL-Metalle: Grundwerkstoffe (11.01.2023)
UBA ELASTOM (16.03.2016)
DVGW W 270 (01.11.2007)

Date of Expiry / File No.
Ablaufdatum / Aktenzeichen

20.06.2028 / 22-0012-WNV

03.04.2023 Fk A-1/2

Date, Issued by, Sheet, Head of Certification Body
Datum, Bearbeiter, Blatt, Leiter der Zertifizierungsstelle



Deutsche
Akkreditierungsstelle
D-ZE-16028-01-05

DVGW CERT GmbH
Zertifizierungsstelle

Josef-Wirmer-Str. 1-3
53123 Bonn

Tel. +49 228 91 88 - 888
Fax +49 228 91 88 - 993

www.dvgw-cert.com
info@dvgw-cert.com

Type <i>Typ</i>	Technical Data <i>Technische Daten</i>	Remarks <i>Bemerkungen</i>
VICTORIA	Pressure rating: PN 10/16 Nominal diameter: DN 25	
VICTORIA	Pressure rating: PN 10/16 Nominal diameter: DN 40	
VICTORIA	Pressure rating: PN 10/16 Nominal diameter: DN 50	
VICTORIA	Pressure rating: PN 10/16 Nominal diameter: DN 65	
VICTORIA	Pressure rating: PN 10/16 Nominal diameter: DN 80	
VICTORIA	Pressure rating: PN 10/16 Nominal diameter: DN 100	
VICTORIA	Pressure rating: PN 10/16 Nominal diameter: DN 125	
VICTORIA	Pressure rating: PN 10/16 Nominal diameter: DN 150	
VICTORIA	Pressure rating: PN 10/16 Nominal diameter: DN 200	
VICTORIA	Pressure rating: PN 10 Nominal diameter: DN 250	
VICTORIA	Pressure rating: PN 10 Nominal diameter: DN 300	
VICTORIA	Pressure rating: PN 10 Nominal diameter: DN 350	
VICTORIA	Pressure rating: PN 10 Nominal diameter: DN 400	
VICTORIA	Pressure rating: PN 19 Nominal diameter: DN 450	
VICTORIA	Pressure rating: PN 10 Nominal diameter: DN 500	
VICTORIA	Pressure rating: PN 10 Nominal diameter: DN 600	
Type Variation <i>Ausführungsvariante</i>	Explanations <i>Erläuterungen</i>	
480; R480	without drive	
481; R481	with pneumatic drive	
487; R487	with manual drive	
488; R488	with electric drive	