

Product

Name	FlipTube®
Part Numbers	98000236 (transparent) 98000405 (yellow) 98000406 (green) 98000407 (red) 98000408 (blue) 98000554 (black)

Dimensions

Volume	1.5 ml
Inner Diameter	8.2 mm
Outer Diameter	10 mm
Height	39.0 mm

Material

Polymer type	Virgin Polypropylene (PP)
Properties	Autoclavable Non sterile DNase/RNase certifications on request Visit www.fliptube.biz for a list of chemical compatibilities

Features

- Easy one hand operation, even when standing in a rack
- Graduated (0.1ml, 0.5ml, 1ml, 1.5ml)
- Large frosted writing surfaces on both top and side
- Piercing area in lid
- Manufactured in clean rooms
- High thermal and chemical resistivity
- Stands centrifugation to 20'000 g, fits all standard centrifuges
- Available in bags of 500 pcs.

Storage conditions

Store in a dry place. Do not expose to temperatures above 50 °C and below -30 °C during storage.

Shipping information

- Shipment & Carrier: Fixed by the customer
- Weight per pallet: 180 kg
- Height of one pallet: approx. 2m
- Amount per pallet: 160'000 pcs.

May 2009/pt