

DVGW type examination certificate

DVGW-Baumusterprüfzertifikat

DW-6201CL0241

Registration Number
Registriernummer

Field of Application <i>Anwendungsbereich</i>	products of water supply <i>Produkte der Wasserversorgung</i>
Owner of Certificate <i>Zertifikatinhaber</i>	GEMÜ Gebr. Müller Apparatebau GmbH & Co. KG Fritz-Müller-Straße 6-8, D-74653 Ingelfinden
Distributor <i>Vertreiber</i>	GEMÜ Gebr. Müller Apparatebau GmbH & Co. KG Fritz-Müller-Straße 6-8, D-74653 Ingelfinden
Product Category <i>Produktart</i>	valves for water supply: butterfly valve (6201)
Product Description <i>Produktbezeichnung</i>	centric butterfly valve (Wafer, Lug respectively U-form) for the drinking water supply
Model <i>Modell</i>	VICTORIA
Test Reports <i>Prüfberichte</i>	laboratory control test: A0 007/17 from 13.04.2017 (TZW) type testing: A0 001/09 + A0 002/09 from 20.06.2010 (TZW) UBA-Guideline: KA 0091/13 from 22.04.2016 (TZW) hygienic testing: MO 006/13 from 09.08.2016 (TZW) UBA-Guideline: K-270239-16-Ko from 02.05.2016 (TZW)
Test Basis <i>Prüfgrundlagen</i>	DVGW W 363-(P) (01.06.2010) DIN EN 1074-1 (01.07.2000) DIN EN 1074-2 (01.07.2004) UBA METALLE (15.03.2017) UBA ELASTOM (16.03.2016) DVGW W 270 (01.11.2007)
Date of Expiry / File No. <i>Ablaufdatum / Aktenzeichen</i>	20.06.2023 / 18-0170-WNV

10028-04-A-DE

26.04.2018 GI A-1/2

Date, Issued by, Sheet, Head of Certification Body
Datum, Bearbeiter, Blatt, Leiter der Zertifizierungsstelle

DVGW CERT GmbH is an accredited body by DAkkS according to DIN EN ISO/IEC 17065:2013 for certification of products for energy and water supply industry.

DVGW CERT GmbH ist von der DAkkS nach DIN EN ISO/IEC 17065:2013 akkreditierte Stelle für die Zertifizierung von Produkten der Energie- und Wasserversorgung



DVGW CERT GmbH
Zertifizierungsstelle

Josef-Wirmer-Str. 1-3
53123 Bonn

Tel. +49 228 91 88 - 888

Fax +49 228 91 88 - 993

www.dvgw-cert.com
info@dvgw-cert.com

Type <i>Typ</i>	Technical Data <i>Technische Daten</i>	Remarks <i>Bemerkungen</i>
VICTORIA	pressure rating: PN 10/16 nominal diameter: DN 25	
VICTORIA	pressure rating: PN 10/16 nominal diameter: DN 40	
VICTORIA	pressure rating: PN 10/16 nominal diameter: DN 50	
VICTORIA	pressure rating: PN 10/16 nominal diameter: DN 65	
VICTORIA	pressure rating: PN 10/16 nominal diameter: DN 80	
VICTORIA	pressure rating: PN 10/16 nominal diameter: DN 100	
VICTORIA	pressure rating: PN 10/16 nominal diameter: DN 125	
VICTORIA	pressure rating: PN 10/16 nominal diameter: DN 150	
VICTORIA	pressure rating: PN 10/16 nominal diameter: DN 200	
VICTORIA	pressure rating: PN 10 nominal diameter: DN 250	
VICTORIA	pressure rating: PN 10 nominal diameter: DN 300	
VICTORIA	pressure rating: PN 10 nominal diameter: DN 350	
VICTORIA	pressure rating: PN 10 nominal diameter: DN 400	
VICTORIA	pressure rating: PN 19 nominal diameter: DN 450	
VICTORIA	pressure rating: PN 10 nominal diameter: DN 500	
VICTORIA	pressure rating: PN 10 nominal diameter: DN 600	
Type Variation <i>Ausführungsvariante</i>	Explanations <i>Erläuterungen</i>	
480	without drive	
481	with pneumatic drive	
487	with manual drive	
488	with electric drive	