

GEMÜ 1573

Switching power supply unit

EN

Technical information



All rights including copyrights or industrial property rights are expressly reserved.

Keep the document for future reference.

© GEMÜ Gebr. Müller Apparatebau GmbH & Co. KG
01.06.2021

Overview of combination variants

GEMÜ 1573 power supply unit

The GEMÜ 1573 switching power supply unit converts unstable input voltages from 100 to 240 V AC from the supply system into a continuous DC voltage. Motorized actuators and a multitude of other devices can be supplied with an output voltage of 24 V DC. Power supply units with a voltage of 48 V DC are available for GEMÜ servoDrive actuators. Several actuators or devices can be supplied by a power supply unit, depending on the size of the power supply unit.

24 V power supply units

Designation	Item number
5 A power supply unit	88660400
10 A power supply unit	88660401

Actuator type	Actuator size	Number with 5 A power supply unit	Number with 10 A power supply unit
eSyLite	1	2	4
eSyLite	3	1	2
eSyStep	0	6	12
eSyStep	1	2	4
eSyDrive	0	3	6
eSyDrive	1	2	4
eSyDrive	2	1	2
C53 iComLine	2	5	10

48 V power supply units

Designation	Item number
5 A power supply unit	88667799
10 A power supply unit	88667801

Valve type	Actuator size	Number with 5 A power supply unit	Number with 10 A power supply unit
F60	3	1	2
F60	4	-	1
567 servoDrive	all	-	1



GEMÜ Gebr. Müller Apparatebau GmbH & Co. KG
Fritz-Müller-Straße 6–8, 74653 Ingelfingen-Criesbach, Germany
Phone +49 (0) 7940 1230 · info@gemue.de
www.gemu-group.com

Subject to alteration

06.2021