

GEMÜ 650TL

Manuell betätigtes Membranventil
Manually operated diaphragm valve

DE

Sonderdokumentation

99100490 (0TL), 99100491 (1TL), 99100492 (2TL)

EN

Special Documentation

99100490 (0TL), 99100491 (1TL), 99100492 (2TL)



1 Sonderdokumentation 650TL / Special documentation 650TL

Bei dieser Sonderversion kann, entgegen der Standard-Dokumentation, die Geschlossen-Position des Handrads und die Offen-Position des pneumatischen Antriebs abgefragt werden. Die restlichen Funktionen entsprechen der Standard-Dokumentation.

Die im Kapitel 11.6 beschriebenen Näherungsinitiatoren für den Pneumatikkolben 1 und das Handrad 2 werten die oben genannten Positionen aus.

Antriebsmaße							
AG	MG	A	A1	A2	B	B1	G
0	8	146	26,5	-	42	32	G 1/8
1	10	196	37,0	27	60	-	G 1/8
2	25	282	51,0	24	114	-	G 1/4

Maße in mm

AG = Antriebsgröße

MG = Membrangröße

With this special version, contrary to the standard documentation, the closed position of the handwheel and the open position of the pneumatic actuator can be queried. The remaining functions correspond to the standard documentation.

The proximity switches for pneumatic piston 1 and handwheel 2 described in chapter 11.6 evaluate the above-mentioned positions.

Actuator dimensions							
AG	MG	A	A1	A2	B	B1	G
0	8	146	26.5	-	42	32	G 1/8
1	10	196	37.0	27	60	-	G 1/8
2	25	282	51.0	24	114	-	G 1/4

Dimensions in mm

AG = actuator size

MG = diaphragm size



Änderungen vorbehalten
Subject to alteration
02.2019 | 88614708

