

GEMÜ 1220, 1221, 1222, 1223, 1224

Cable plug

Connector: Design A and B (to DIN EN 175301-803 or industrial standard) with seal, with or without light

Basic version: Terminals, without bridge rectifier, without interference suppressor, 230V 50/60 Hz, (glow lamp)

Material: PA, Polyamide



GEMÜ 1220
Design A
DIN EN 175301-803
with light



GEMÜ 1221
Design A
DIN EN 175301-803
without light



GEMÜ 1222
Design B
Industrial standard
with light



GEMÜ 1223
Design B
Industrial standard
without light



GEMÜ 1224
Design B
DIN EN 175301-803
with/without light

Order data

Type / Version	Code
1220 / Design A (wide), to DIN EN 175301-803 Socket with light	1220
1221 / Design A (wide), to DIN EN 175301-803 Socket without light	1221
1222 / Design B (narrow), Industrial standard Socket with light	1222
1223 / Design B (narrow), Industrial standard Socket without light	1223
1224 / Design B (narrow), to DIN EN 175301-803 Socket with / without light	1224

Field bus	Code
without	000

Accessory	Code
Accessory	Z

Connection	Code
Terminals	0
Plug, M12, without interference suppressor, without bridge rectifier (only voltage 24V) (Type 1220,1221,1223)	2

Light	Code
Without light	0
Glow lamp (for $\geq 120V$)	1
Incandescent lamp (for $\leq 48V$)	2
LED red (for 24 V DC)	3
LED green (for 24 V DC)	4
LED yellow (for 24 V DC)	5

Bridge rectifier	Code
Without bridge rectifier	0
With bridge rectifier	1

Interference suppressor	Code
Without interference suppressor	0
Erasing diode (only DC)	1
Varistor (only AC)	2

Voltage	Code
24 V	24
48 V	48
120 V	120
230 V	230

Frequency	Code
AC 50/60 Hz	50/60
DC voltage	DC

Optional version	K-Nr.
Version without paint adhesion interfering substances	0101

Order example	1220	000	Z	0	4	0	0	24	DC	
Type/Version (Code)	1220									
Field bus (Code)		000								
Accessory (Code)			Z							
Connection (Code)				0						
Light (Code)					4					
Bridge rectifier (Code)						0				
Interference suppressor (Code)							0			
Voltage (Code)								24		
Frequency (Code)									DC	
Optional version (K-No.)										

Note: The plug of the DC version with bridge rectifier has reverse battery protection.

For further accessories and other products, please see our Product Range catalogue and Price list. Contact GEMÜ.

GEMÜ® VALVES, MEASUREMENT
AND CONTROL SYSTEMS

