



Plastic ball valve GEMÜ S717

Areas of application

- Industrial water treatment

Features

- Long life
- Reliable
- Simple to install

Description

Ball valve made of thermoplastic material.
Ergonomic grip with non-slip rubber coating
for safe operation.

Technical specifications

- **Media temperature*:**
0 to 60 °C
- **Ambient temperature:**
0 to 60 °C
- **Operating pressure:**
0 to 16 bar
- **Nominal sizes*:**
DN 10 to 100
- **Connection types:**
Union end | Flange | Thread |
Solvent cement socket | Spigot
- **Body materials:**
PVC-U, grey | PP-H, grey
- **Seal materials:**
EPDM | FKM

* depending on version and/or operating parameters

Applications


- Swimming pool processes
- Irrigation
- Water treatment
- Distribution of liquids
- Fish farming
- Agriculture

Flexible

Max. operating pressure
16 bar (depending on
version)

Practical

The grip is also used as a
regulating key for adapting
the seal carrier or ball torque



Variable

Choice of various
connection options

Wide range of nominal sizes

Nominal size DN 10 to 100