

Produktlinie

				
	GEMÜ BB02	GEMÜ B22	GEMÜ B42	GEMÜ B52
Antriebsart				
ohne Antrieb	●	-	-	-
manuell	-	●	-	-
pneumatisch	-	-	●	-
elektromotorisch	-	-	-	●
Nennweiten	DN 8 bis 100	DN 8 bis 100	DN 8 bis 100	DN 8 bis 100
Medientemperatur	-40 bis 180 °C	-40 bis 180 °C	-40 bis 180 °C	-40 bis 180 °C
Betriebsdruck	0 bis 63 bar	0 bis 63 bar	0 bis 63 bar	0 bis 63 bar

CRN	Approval date / Datum der Zulassung	Expiry date / Ablaufdatum	Province/Territory / Bundesland	Safety Authority / Sicherheitsbehörde
0C3023.31	27. February 2024	20. February 2034	British Columbia	TSBC
0C3023.32	20. May 2025	20. February 2034	Alberta	ABSA
0C3023.3	20. February 2024	20. February 2034	Saskatchewan	TSASK
0C3023.34	28. March 2024	20. February 2034	Manitoba	Office of fire commission
0C3023.35	10. July 2024	20. February 2034	Ontario	TSSA
0C3023.36	12. December 2024	12. December 2034	Quebec	RBQ
0C3023.37	03. Aug 24	12. February 2034	ACI central	New Brunswick
0C3023.38	12. March 2024	12. February 2034	ACI central	Nova Scotia
0C3023.39	08. March 2024	12. February 2034	ACI central	Prince Edward Island
0C3023.30	11. March 2024	12. February 2034	ACI central	Newfoundland
0C3023.3N	03.08.2024	12. February 2034	ACI central	Nunavut
0C3023.35	11. March 2024	12. February 2034	ACI central	Northwest Territories
0C3023.3Y	03.08.2024	12. February 2034	ACI central	Yukon

Design Code: ASME B31.3, 2022 Ed.
Corrosion Allowance: 0mm
Radiography: N/A
PWHT: N/A

BB02	Availability Connection code / DN							
	Spigot				Threaded Socket		Flange	
DN	17	19	59	60	1	31	8	11
8	-	PN63	-	PN63	PN63	PN63	-	-
10	PN63	PN63	-	PN63	PN63	PN63	-	-
15	PN63	PN63	PN63	PN63	PN63	PN63	-	PN40
20	PN63	PN63	PN63	PN63	PN63	PN63	-	PN40
25	PN63	PN63	PN63	PN63	PN63	PN63	-	PN40
32	PN63	PN63	-	PN63	PN63	PN63	-	PN40
40	PN63	PN63	PN63	PN63	PN63	PN63	-	PN40
50	PN63	PN63	PN63	PN63	PN63	PN63	-	PN40
65	PN40	PN40	PN40	PN40	PN40	PN40	PN16	-
80	PN40	PN40	PN40	PN40	PN40	PN40	PN16	-
100	PN25	PN25	PN25	PN25	PN25	PN25	PN16	-

Material	
Body	1.4408 / CF8M UNS J92900
Connection	1.4409 / CF3M UNS J92800
Bolting	A2-70 / AISI 304/L

Pressure (bar)	Temp (C)				
	Ambient	100	150	200	250
PN63	63	63	57.3	53.1	50.1
PN40	40	40	36.3	33.7	31.8
PN16	16	16	14.5	13.4	12.7

ref: KY193285

SOR-BB02-REV0