

GEMÜ R480 Victoria

Butterfly valve with bare shaft



Features

- Low torques thanks to PTFE coated bushes
- Bubble tight sealing, in accordance with EN 12266-1/P12, leak rate A
- Liner material is easy to read when installed
- Sleek disc design for higher Kv values
- Robust body coating comparable to ISO 12944-6 C5

Description

The GEMÜ R480 Victoria soft seated metal butterfly valve is equipped with a bare shaft with top flange in accordance with EN ISO 5211. The butterfly valve is available in nominal sizes DN 50 to 300 and in standardized installation lengths ISO 5752/20 | EN 558-1/20 | API 609 category A (DIN 3202 K1) in wafer and lug body versions.

Technical specifications

- **Media temperature:** 14 to 302 °F
- **Ambient temperature:** 14 to 158 °F
- **Operating pressure:** 0 to 232 psi
- **Nominal sizes:** 2" (DN 50) to 12" (DN 300)
- **Body configurations:** Lug | Wafer
- **Connection standards:** AS | ASME | BS | DIN | EN | ISO | JIS
- **Body materials:** EN-GJS-400-15, SG iron material | EN-GJS-400-18-LT, SG iron material
- **Body coating:** Epoxy
- **Liner materials:** EPDM | FKM | NBR | SBR, abrasion resistant | Silicone
- **Disc materials:** 1.4408, investment casting material | 1.4408, polished investment casting material | 1.4469, Duplex cast steel material | EN-GJS-400-15, SG iron material
- **Disc coating:** Epoxy | Halar® | Rilsan®
- **Conformities:** ACS | ATEX | Belgaqua | DNV GL | DVGW Gas | EAC | FDA | Functional safety | NSF | Oxygen | Regulation (EC) No. 1935/2004 | TA Luft (German Clean Air Act) | WRAS

Technical data depends on the respective configuration



further information
webcode: GW-R480



Product line



GEMÜ R480
Victoria

GEMÜ R481
Victoria


GEMÜ R487
Victoria

GEMÜ R488
Victoria

Operation				
With bare shaft	●	-	-	-
Manual	-	-	●	-
pneumatic	-	●	-	-
Motorized	-	-	-	●
Nominal sizes	2" (DN 50) to 12" (DN 300)	2" (DN 50) to 12" (DN 300)	2" (DN 50) to 12" (DN 300)	2" (DN 50) to 12" (DN 300)
Media temperature	14 to 302 °F	14 to 302 °F	14 to 302 °F	14 to 302 °F
Operating pressure	0 to 232 psi	0 to 232 psi	0 to 232 psi	0 to 232 psi
Connection types				
Flange (lug)	●	●	●	●
Flange (wafer)	●	●	●	●
Conformities				
ACS	●	●	●	●
ATEX	●	●	●	●
Belgaqua	●	●	●	●
DNV GL	●	●	●	●
DVGW Gas	●	●	●	●
EAC	●	●	●	●
FDA	●	●	●	●
Functional safety	●	●	●	●
NSF	●	●	●	●
Oxygen	●	●	●	●
Regulation (EC) No. 1935/2004	●	●	●	●
TA Luft (German Clean Air Act)	●	●	●	●
WRAS	●	●	●	●

Product description

Construction



Item	Name	Materials
1	Body	SG iron 5.3106, epoxy coated (RAL 5021)
2	Shaft	1.4021
3	Axis	1.4021
4	Disc	Various materials (see order data)
5	Liner	Various materials (see order data)
6	Threaded plug	1.4408
7	O-ring	NBR
8	Support rings	PTFE
9	Hexagon head bolts	Stainless steel A2-70
0	Earthing kit for ATEX version	
0-1	Cable lug (ATEX version)	
0-2	Stranded wire (ATEX version)	
10	CONEXO RFID chip (see "GEMÜ CONEXO", page 22)	

Product conformities

	Approved designs			Special function (code)
	Disc material	Liner material	Liner fixing	
Drinking water				
ACS	CF8M, 1.4408 (code A) CF8M, 1.4408 polished (code B) Super Duplex, 1.4469 (code D) EN-GJS-400-15 (GGG-40), epoxy coated (code E) EN-GJS-400-15, GGG40 Rilsan® PA11 coated (code R)	EPDM (code W)	All versions	A
Belgaqua	CF8M, 1.4408 (code A) CF8M, 1.4408 polished (code B) Super Duplex, 1.4469 (code D)	EPDM (code W)	Loose (code L)	B
DVGW Water	CF8M, 1.4408 (code A) CF8M, 1.4408 polished (code B)	EPDM (code W)	Loose (code L)	D
NSF	CF8M, 1.4408 (code A) Super Duplex, 1.4469 (code D)	EPDM (code W)	All versions	N
WRAS	CF8M, 1.4408 (code A) CF8M, 1.4408 polished (code B) Super Duplex, 1.4469 (code D)	EPDM (code W)	All versions	W
Food				
FDA	CF8M, 1.4408 (code A) CF8M, 1.4408 polished (code B) Super Duplex, 1.4469 (code D)	EPDM-AB/E (code G) EPDM-AB/W (code I) EPDM, white (code M) NBR (W) (code U) EPDM-HT (code Z)	All versions	no order code required
Regulation 1935/2004	CF8M, 1.4408 polished (code B)	EPDM, white (code M) NBR (W) (code U) EPDM-AB/W (code I)	All versions	no order code required
Gas				
DVGW Gas	CF8M, 1.4408 (code A) CF8M, 1.4408 polished (code B)	NBR (code J)	Loose (code L)	G
Oxygen				
Oxygen	CF8M, 1.4408 (code A) CF8M, 1.4408 polished (code B)	EPDM (code E)	All versions	O
Ship approval				
DNV GL	All materials	All materials	All versions	S
Explosion protection				
ATEX internal and ex- ternal	CF8M, 1.4408 (code A) CF8M, 1.4408 polished (code B) Super Duplex, 1.4469 (code D) 2.0975 / CC333G (code G) 1.4435 / ASTM A351 / CF3M / AISI 316L (code I)	EPDM (code E)	All versions	Y
ATEX external	All materials	All materials	All versions	X

	Approved designs			Special function (code)
	Disc material	Liner material	Liner fixing	
Functional safety				
Functional safety	All materials	All materials	All versions	S

Other features are not relevant for the product conformities

Availabilities - Type of design

Type of design (code) ¹⁾	
0101	All except liner code V, EPDM-HT code Z and silicone code S
1782	Only disc material code B

All other types of design can be freely combined.

1) **Type of design**

Code 0101: Media wetted area cleaned to ensure suitability for paint applications, parts sealed in plastic bag

Code 1782: Stainless steel valve disc, mechanically polished to 1.6 µm and electropolished, spigot internally polished to 1.6 µm

Order data

Other configurations available on request. Please check the availability with GEMÜ before ordering.

Products ordered with **bold marked ordering options** are so-called preferred series. Depending on the nominal size, these are available more quickly.

Order codes

1 Type	Code
Butterfly valve, bare shaft, body with C5-M coating (min. 250µm) and integrated leakage groove, blow-out proof shaft with dust protection, multiple bearings through PTFE bushing, multiple sealing system with insertion slope, material easy to read when installed	R480

2 DN	Code
DN 50	50
DN 65	65
DN 80	80
DN 100	100
DN 125	125
DN 150	150
DN 200	200
DN 250	250
DN 300	300

3 Body configuration	Code
Flange-mounted design (lug), face-to-face dimension FTF EN 558 series 20	L
Intermediate flange design (wafer), face-to-face dimension FTF EN 558 series 20	W

4 Operating pressure	Code
3 bar	0
6 bar	1
10 bar	2
16 bar	3

5 Connection type	Code
PN 6 / flange EN 1092, face-to-face dimension FTF EN 558 series 20	1
PN 10 / flange EN 1092, face-to-face dimension FTF EN 558 series 20	2
PN 16 / flange EN 1092, face-to-face dimension FTF EN 558 series 20	3
ANSI B16.5, Class 150, face-to-face dimension FTF EN 558 series 20	D
Flange BS 10 Tab E, face-to-face dimension FTF EN 558, series 20	S
Flange AS 2129 Tab D, face-to-face dimension FTF EN 558, series 20	T
Flange AS 2129 Tab E, face-to-face dimension FTF EN 558, series 20	U
Flange BS 10 Tab D, face-to-face dimension FTF EN 558, series 20	H
JIS 10 K, face-to-face dimension FTF EN 558, series 20	G

5 Connection type	Code
JIS 16 K, face-to-face dimension FTF EN 558, series 20	J

6 Body material	Code
EN-GJS-400-15 (GGG-40), epoxy-coated 250 µm	2
EN-GJS-400-18-LT (GGG-40.3), epoxy coated 250 µm	3

7 Disc material	Code
1.4408	A
1.4408, polished, roughness Ra 0.6-3.2, except disc marking	B
1.4408, Halar coated	C
1.4469, super duplex	D
EN-GJS-400-15 (GGG-40), epoxy coated	E
EN-GJS-400-15 (GGG-40), HALAR coated	P
EN-GJS-400-15 (GGG-40), RILSAN PA11 coated	R
2.0975/CC333G	G
1.4435 / ASTM A351 / CF3M / AISI 316L	I

8 Shaft material	Code
1.4021	1

9 Shut-off seal material	Code
EPDM-HT-AB/T (abrasion resistant)	B
EPDM	E
SBR-AB/P (abrasion resistant)	F
EPDM-AB/E (abrasion resistant)	G
CSM	H
EPDM (FDA certification), white-AB/W	I
NBR (DVGW Gas certification)	J
EPDM (FDA certification), white	M
NBR	N
FKM +	O
EPDM-SHT (steam)	T
NBR (FDA certification), white	U
FKM	V
EPDM (drinking water compliant)	W
EPDM-HT (FDA certification)	Z

10 Liner fixing	Code
Liner bonded into body	B
Loose liner	L

11 Type of design	Code
Without	
Media wetted area cleaned to ensure suitability for paint applications, parts sealed in plastic bag	0101
Valve free of oil and grease, media wetted area cleaned and packed in PE bag	0107

Order data

11 Type of design	Code
Stainless steel valve disc, mechanically polished to 1.6 µm and electropolished, spigot internally polished to 1.6 µm	1782
Butterfly valve body powder coated, RAL 5015, sky blue	1892
Butterfly valve body powder coated, RAL 1023, traffic yellow	1925
Mounting parts in A4 quality. Caution! Danger of galling! Customer must provide for this!	5143
Thermal separation between actuator and valve body via mounting kit	5222
Thermal separation between actuator and valve body via dew point barrier	5226
Alu product label, black anodized, lasered marking, riveted to the body	6061
12 Special version	Code
Without	
ACS certification	A

12 Special version	Code
BELGAQUA certification	B
DVGW Water certification	D
European origin	E
DVGW Gas approval (only valid in conjunction with a suitable manual, pneumatic or motorized actuator)	G
NSF 61 water certification	N
Oxygen	O
DNV GL certification	S
WRAS certification	W
ATEX certification	X
ATEX certification (in the piping system)	Y
13 CONEXO	Code
Without	
Integrated RFID chip for electronic identification and traceability	C

Order example - standard version

Order option	Code	Description
1 Type	R480	Butterfly valve, bare shaft, body with C5-M coating (min. 250µm) and integrated leakage groove, blow-out proof shaft with dust protection, multiple bearings through PTFE bushing, multiple sealing system with insertion slope, material easy to read when installed
2 DN	80	DN 80
3 Body configuration	W	Intermediate flange design (wafer), face-to-face dimension FTF EN 558 series 20
4 Operating pressure	3	16 bar
5 Connection type	3	PN 16 / flange EN 1092, face-to-face dimension FTF EN 558 series 20
6 Body material	2	EN-GJS-400-15 (GGG-40), epoxy-coated 250 µm
7 Disc material	A	1.4408
8 Shaft material	1	1.4021
9 Shut-off seal material	E	EPDM
10 Liner fixing	L	Loose liner
11 Type of design		Without
12 Special version		Without
13 CONEXO		Without


Technical data

Medium

Working medium: Gaseous and liquid media which have no negative impact on the physical and chemical properties of the disc and seat material.

Temperature

Media temperature: 14 – 302 °F
Depending on the liner and disc material or the type of liner fixing



FPM material not suitable for water/steam applications above 212 °F, Observe Pressure/Temperature diagram.

Ambient temperature: 14 – 158 °F


Storage temperature: 32 – 104 °F

Pressure

Operating pressure: 0 – 232 psi
Use (installation) as end-of-line valve
DN 50 – 200: 145 psi
DN 250, 300: 87 psi

Vacuum: These values apply to room temperature and air. The values may deviate for other media and other temperatures.

Pressure/temperature diagram:



Pressure rating:

PN 3
PN 6
PN 10
PN 16

Cv values:

DN	Kv values at opening angle							
	20°	30°	40°	50°	60°	70°	80°	90°
50	3.51	10.53	23.40	38.61	76.05	128.70	145.08	146.25
65	10.53	17.55	35.10	74.88	138.06	228.15	250.38	259.74
80	22.23	46.80	77.22	136.89	229.32	375.57	413.01	424.71
100	33.93	87.75	160.29	249.21	369.72	569.79	683.28	723.06
125	56.16	117.00	216.45	368.55	643.50	1047.15	1240.20	1310.40
150	70.20	175.50	328.77	526.50	923.13	1497.60	1907.10	2024.10
200	128.70	328.77	552.24	888.03	1731.60	3369.60	4340.70	4563.00
250	234.00	519.48	863.46	1392.30	2468.70	4539.60	6060.60	6329.70
300	292.50	797.94	1240.20	1953.90	3650.40	7441.20	10085.40	10448.10

Cv values in gpm

When the opening angle is below 30° no regulation should be made!

Product conformity

Pressure Equipment Directive:

2014/68/EU

Food:

FDA
Regulation (EC) No. 1935/2004

Drinking water:

DVGW
ACS
WRAS
Belgaqua
NSF

Oxygen:

BAM compliant, the product is suitable for application with oxygen

Gas:

DVGW

Ship approval:

DNVGL

Explosion protection:

ATEX (2014/34/EU), order code Special version X and Y

ATEX marking:

Special function code X

Gas:  II -/2 G Ex h -/IIB T6...T3 -/Gb XDust:  II -/2D Ex h -/IIIC T150°C -/Db X

Special function code Y

Gas:  II 2 G Ex h IIC/IIB T6 ... T3 Gb XDust:  II 2 D Ex h IIIC T150 °C Db X**SIL:****Product description:**

GEMÜ butterfly valve R480 Victoria®

Type of valve:

A

Safety function:

The safety function of the Butterfly Valve is to open on trip, close on trip, or close with a tight shutoff on trip.

HFT (Hardware Fault Tolerance):

0

MTTR (Mean Time To Restoration):

48 hours

Mechanical data**Torques:**


DN	PS		
	43.5 psi (3 bar)	145 psi (10 bar)	232 psi (16 bar)
50	-	-	9.0
65	-	-	15.0
80	-	-	25.0
100	-	-	40.0
125	-	-	60.0
150	-	-	100.0
200	145.0	-	242.0
250	152.0	310.0	-
300	245.0	330.0	-

Torques in Nm

Working medium water (68 °F) and optimal operating conditions


Dimensions

Actuator flange



DN	$\square G$	ϕa	ISO 5211	$\phi b1$	$\phi y1$	$\phi b2$	$\phi y2$	E
50	0.35	2.56	F03 F05	1.42	0.24	1.97	0.28	0.67
65	0.43	2.56	F03 F05	1.42	0.24	1.97	0.28	0.67
80	0.43	2.56	F05	1.97	0.28	-	-	0.67
100	0.55	2.56	F05	1.97	0.28	-	-	0.67
125	0.67	3.54	F05 F07	1.97	0.28	2.76	0.35	0.91
150	0.67	3.54	F05 F07	1.97	0.28	2.76	0.35	0.91
200	0.87	4.92	F07 F10	2.76	0.35	4.02	0.43	1.34
250	0.87	4.92	F07 F10	2.76	0.35	4.02	0.43	1.34
300	0.87	4.92	F07 F10	2.76	0.35	4.02	0.43	1.34


Dimensions in inch

Body**Wafer body configuration**

DN	PS	A	B	B1	FTF	$\varnothing D$	$\varnothing D1$	F	H	$\varnothing S$	I
50	16	4.72	7.17	2.44	1.69	3.54	4.65	0.28	1.14	2.05	0.20
65	16	5.39	8.58	3.19	1.81	4.25	5.24	0.28	1.89	2.64	0.39
80	16	5.71	9.09	3.43	1.81	5.12	5.55	0.28	2.68	3.23	0.71
100	16	6.54	10.67	4.13	2.05	5.91	6.42	0.28	3.46	4.02	0.98
125	16	7.36	11.97	4.61	2.20	6.89	4.72	0.35	4.49	5.00	1.38
150	16	7.87	13.07	5.20	2.20	8.15	5.08	0.35	5.55	5.98	1.89
200	16	9.45	16.26	6.81	2.36	10.35	6.18	0.43	7.60	7.95	2.80
250	10	10.43	18.35	7.91	2.68	12.48	7.28	0.43	9.53	9.92	3.62
300	10	11.42	20.91	9.49	3.07	14.41	6.46	0.43	11.46	11.89	4.41

Dimensions in inch

Connections



Connection EN1092, EN1759

DN	INCH	Connection (code)															
		EN1092-1 PN6 (code 1)				EN1092-1 PN10 (code 2)				EN1092-1 PN16 (code 3)				EN1759/CL150 (code D)			
DIN	ASME	w°	n	ØG	y	w°	n	ØG	y	w°	n	ØG	y	w°	n	ØG	y
50	2"	90	4	4.33	0.55	90	4	4.92	0.71	90	4	4.92	0.71	90	4	4.75	0.75
65	2½"	90	4	5.12	0.55	90	8	5.71	0.71	90	8	5.71	0.71	90	4	5.50	0.75
80	3"	90	4	5.91	0.71	45	8	6.30	0.71	45	8	6.30	0.71	90	4	6.00	0.75
100	4"	90	4	6.69	0.71	45	8	7.09	0.71	45	8	7.09	0.71	45	8	7.50	0.75
125	5"	45	8	7.87	0.71	45	8	8.27	0.71	45	8	8.27	0.71	45	8	8.50	0.87
150	6"	45	8	8.86	0.71	45	8	9.45	0.87	45	8	9.45	0.87	45	8	9.50	0.87
200	8"	45	8	11.02	0.71	45	8	11.61	0.87	30	12	11.61	0.87	45	8	11.75	0.87
250	10"	30	12	13.19	0.71	30	12	13.78	0.87	30	12	13.98	1.02	30	12	14.25	1.00
300	12"	30	12	15.55	0.87	30	12	15.75	0.87	30	12	16.14	1.02	30	12	17.00	1.00

Dimensions in inch


n = number of bolts

Connection AS2129, BS10

DN	INCH	Connection (code)															
		AS 2129 D (code T)				AS 2129 E (code U)				BS10 D (code H)				BS10 E (code S)			
DIN	ASME	w°	n	ØG	y	w°	n	ØG	y	w°	n	ØG	y	w°	n	ØG	y
50	2"	90	4	4.49	0.71	90	4	4.49	0.71	90	4	4.50	0.69	90	4	4.50	0.69
65	2½"	90	4	5.00	0.71	90	4	5.00	0.71	90	4	5.00	0.69	90	4	5.00	0.69
80	3"	90	4	5.75	0.71	90	4	5.75	0.71	90	4	5.75	0.69	90	4	5.75	0.69
100	4"	90	4	7.01	0.71	45	8	7.01	0.71	90	4	7.00	0.69	45	8	7.00	0.69
125	5"	45	8	8.27	0.71	45	8	8.27	0.71	45	8	8.25	0.69	45	8	8.25	0.69
150	6"	45	8	9.25	0.71	45	8	9.25	0.87	45	8	9.25	0.69	45	8	9.25	0.81
200	8"	45	8	11.50	0.71	45	8	11.50	0.87	45	8	11.50	0.69	45	8	11.50	0.81
250	10"	45	8	14.02	0.87	30	12	14.02	0.87	45	8	14.00	0.87	30	12	14.00	0.87
300	12"	30	12	15.98	0.87	30	12	15.98	1.02	30	12	16.00	0.87	30	12	16.00	1.00

Dimensions in inch

n = number of bolts




Connection JIS K10, K16

DN	INCH	Connection (code)							
		JIS-K10 (code G)				JIS-K16 (code J)			
DIN	ASME	w°	n	ØG	y	w°	n	ØG	y
50	2"	90	4	4.72	0.75	45	8	4.72	0.75
65	2½"	90	4	5.51	0.75	45	8	5.51	0.75
80	3"	45	8	5.91	0.75	45	8	6.30	0.91
100	4"	45	8	6.89	0.75	45	8	7.28	0.91
125	5"	45	8	8.27	0.91	45	8	8.86	0.98
150	6"	45	8	9.45	0.91	30	12	10.24	0.98
200	8"	30	12	11.42	0.91	30	12	12.01	0.98
250	10"	30	12	13.98	0.98	30	12	14.96	1.06
300	12"	22,5	16	15.75	0.98	22.5	16	16.93	1.06

Dimensions in inch
n = number of bolts


Lug body configuration



DN	PS	A	B	B1	FTF	ØD	ØD1	F	H	ØS	I
50	16	4.72	7.17	2.44	1.73	3.58	4.57	0.35	1.14	2.05	0.16
65	16	5.39	8.62	3.23	1.81	4.29	4.96	0.35	1.89	2.64	0.39
80	16	5.71	9.21	3.50	1.81	5.16	6.97	0.35	2.68	3.23	0.71
100	16	6.54	10.63	4.09	2.05	6.02	8.15	0.39	3.46	4.02	0.98
125	16	7.36	12.01	4.65	2.20	6.89	9.09	0.39	4.49	5.00	1.42
150	16	7.87	13.11	5.24	2.20	8.19	10.04	0.39	5.55	5.98	1.89
200	16	9.45	16.34	6.89	2.36	10.39	12.80	0.47	7.60	7.95	2.80
250	10	10.43	18.39	7.95	2.68	12.48	15.20	0.43	9.53	9.92	3.62
300	10	11.42	20.91	9.49	3.07	14.41	18.07	0.47	11.46	11.89	4.41

Dimensions in inch

Connections



Connection EN1092, EN1759

DN	INCH	Connection (code)															
		EN1092-1 PN6 (code 1)				EN1092-1 PN10 (code 2)				EN1092-1 PN16 (code 3)				EN1759/CL150 (code D)			
DIN	ASME	w°	n	ØG	y	w°	n	ØG	y	w°	n	ØG	y	w°	n	ØG	y
50	2"	90	4	4.33	M12	90	4	125.0	M16	90	4	4.92	M16	90	4	4.75	5/8"
65	2½"	90	4	5.12	M12	90	4*	145.0	M16	90	8*	5.71	M16	90	4	5.50	5/8"
80	3"	90	4	5.91	M16	45	8	160.0	M16	45	8	6.30	M16	90	4	6.00	5/8"
100	4"	90	4	6.69	M16	45	8	180.0	M16	45	8	7.09	M16	45	8	7.50	5/8"
125	5"	45	8	7.87	M16	45	8	210.0	M16	45	8	8.27	M16	45	8	8.50	3/4"
150	6"	45	8	8.86	M16	45	8	240.0	M20	45	8	9.45	M20	45	8	9.50	3/4"
200	8"	45	8	11.02	M16	45	8	295.0	M20	30	12	11.61	M20	45	8	11.75	3/4"
250	10"	30	12	13.19	M16	30	12	350.0	M20	30	12	13.98	M24	30	12	14.25	7/8"
300	12"	30	12	15.55	M20	30	12	400.0	M20	30	12	16.14	M24	30	12	17.00	7/8"

Dimensions in inch

n = number of bolts

* Standard: 8 holes code 3 (PN16); if 4 holes are required, select code 2 (PN10);

Connection AS 2129, BS10


DN	INCH	Connection (code)															
		AS 2129 D (code T)				AS 2129 E (code U)				BS10 D (code H)				BS10 E (code S)			
DIN	ASME	w°	n	ØG	y	w°	n	ØG	y	w°	n	ØG	y	w°	n	ØG	y
50	2"	90	4	4.49	M16	90	4	4.49	M16	90	4	4.50	5/8"	90	4	4.50	5/8"
65	2½"	90	4	5.00	M16	90	4	5.00	M16	90	4	5.00	5/8"	90	4	5.00	5/8"
80	3"	90	4	5.75	M16	90	4	5.75	M16	90	4	5.75	5/8"	90	4	5.75	5/8"
100	4"	90	4	7.01	M16	45	8	7.01	M16	90	4	7.00	5/8"	45	8	7.00	5/8"
125	5"	45	8	8.27	M16	45	8	8.27	M16	45	8	8.25	5/8"	45	8	8.25	5/8"
150	6"	45	8	9.25	M16	45	8	9.25	M20	45	8	9.25	5/8"	45	8	9.25	3/4"
200	8"	45	8	11.50	M16	45	8	11.50	M20	45	8	11.50	5/8"	45	8	11.50	3/4"
250	10"	45	8	14.02	M20	30	12	14.02	M20	45	8	14.00	3/4"	30	12	14.00	3/4"

Dimensions

DN	INCH	Connection (code)															
		AS 2129 D (code T)				AS 2129 E (code U)				BS10 D (code H)				BS10 E (code S)			
DIN	ASME	w°	n	ØG	y	w°	n	ØG	y	w°	n	ØG	y	w°	n	ØG	y
300	12"	30	12	15.98	M20	30	12	15.98	M24	30	12	16.00	3/4"	30	12	16.00	7/8"

Dimensions in inch

n = number of bolts



Connection JIS K10, JIS K16

DN	INCH	Connection (code)							
		JIS-K10 (code G)				JIS-K16 (code J)			
DIN	ASME	w°	n	ØG	y	w°	n	ØG	y
50	2"	90.0	4	4.72	M16	45.0	8	4.72	M16
65	2½"	90.0	4	5.51	M16	45.0	8	5.51	M16
80	3"	45.0	8	5.91	M16	45.0	8	6.30	M20
100	4"	45.0	8	6.89	M16	45.0	8	7.28	M20
125	5"	45.0	8	8.27	M20	45.0	8	8.86	M22
150	6"	45.0	8	9.45	M20	30.0	12	10.24	M22
200	8"	30.0	12	11.42	M20	30.0	12	12.01	M22
250	10"	30.0	12	13.98	M22	30.0	12	14.96	M24
300	12"	22.5	16	15.75	M22	22.5	16	16.93	M24

Dimensions in inch

n = number of bolts

Add-on components



GEMÜ GDR/GSR

Pneumatic basic quarter turn actuators

The pneumatic basic actuators GEMÜ GSR and GEMÜ GDR are quarter turn actuators with clockwise rotation for Open/Close applications. Single acting (GEMÜ GSR) or double acting versions (GEMÜ GDR) are available. With their standardized connection for pilot valves, position feedback and flanged connection according to ISO 5211, they are suitable for mounting on butterfly valves and ball valves.



GEMÜ ADA/ASR

Pneumatic universal quarter turn actuators

GEMÜ ADA is a pneumatic, double acting and GEMÜ ASR a pneumatic, single acting quarter turn actuator. Both work according to the double piston rack and pinion principle and are suitable for mounting to butterfly valves or ball valves.



GEMÜ DR/SC

Pneumatic premium quarter turn actuators

GEMÜ DR is a pneumatic, double acting and GEMÜ SC a pneumatic, single acting quarter turn actuator. Both work according to the double piston rack and pinion principle and are suitable for mounting to butterfly valves or ball valves.



GEMÜ 9428

Elektromotorischer Schwenkantrieb

Das Produkt ist ein elektromotorisch betriebter Schwenkantrieb. Der Antrieb ist für DC oder AC Betriebsspannungen konzipiert. Eine Handnotbetätigung und eine optische Stellungsanzeige sind serienmäßig integriert. Das Drehmoment in den Endlagen ist erhöht. Das ermöglicht eine an die Armaturen angepasste Schließcharakteristik.



GEMÜ 9468

Elektromotorischer Schwenkantrieb

GEMÜ 9468 ist ein elektromotorisch betriebter Schwenkantrieb. Eine Handnotbetätigung und eine optische Stellungsanzeige sind serienmäßig integriert. Das Drehmoment in den Endlagen ist erhöht. Das ermöglicht eine an die Armaturen angepasste Schließcharakteristik.



GEMÜ J4C

Motorized quarter turn actuator

Der Antrieb J3C ist ein elektromotorisch betriebter Schwenkantrieb. Der Motor ist für DC und AC Betriebsspannungen konzipiert. Eine Handnotbetätigung und eine optische Stellungsanzeige sind serienmäßig integriert. Die Endlagen sind justierbar.



GEMÜ DAHL / SAHL / GHL / VHL

Hand lever

Lockable aluminium or stainless steel hand lever with standard flange acc. to EN ISO 5211 for manual operation (latch positions or continuous) of butterfly valves.



GEMÜ GB

Handwheel with gearbox

Handwheel with gearbox made of aluminium diecasting, GG25 or stainless steel with standard flange acc. to EN ISO 5211 for the manual operation of quarter turn valves. Option with chain wheel or prepared for limit switches.



GEMÜ LSC

Limit switch box for quarter turn actuators

The GEMÜ LSC limit switch box is suitable for mounting to manually and pneumatically operated quarter turn valves. It is also fitted with an optical position indicator for visual confirmation of position.




GEMÜ LSF

Inductive dual sensor for quarter turn valves

The GEMÜ LSF inductive dual sensor is suitable for mounting to manually and pneumatically operated quarter turn valves. It is also fitted with an optical position indicator for visual confirmation of position.

Accessories



GEMÜ RCO

Shaft extension

The RCO shaft extension for quarter turn valves is a distance piece between manually, pneumatically or electrically operated valves. This means that valves can be protected from flooding or better access for operation of the valve can be ensured (also for manual override).



GEMÜ MSC

Mounting kit

The MSC mounting kit is an interface, for the same and different ends, to join flange designs according to ISO 5211. This mounting kit ensures thermal separation of actuator and valve body. It can also be used as height compensation for insulated pipelines. The mounting kit is available in steel, electrogalvanized and stainless steel in an open or closed design.

GEMÜ ADH

Mounting sleeve

The mounting sleeve accessories are available in the square and star geometry designs. These are used for the shaft and hub support for quarter turn actuators. Both sleeves have an internal square drive (please observe stated measurement dimensions here). The sleeve material is sintered metal and they are chemically nickel plated with a surface of 25 µm.

Certificates

Certificate	Standard	Item number
2.1 Certificate of compliance with the order	EN 10204	88039442
2.2 Functionality	EN 10204/EN 12266-2 F20	88439527
2.2 Pressure test	EN 10204, DIN EN 12266 P10, P11, P12	88039443
3.1 Body material	EN 10204	88314529
3.1 Disc material	EN 10204	88314530
3.1 Shaft material		88734227
3.1 Pressure test	EN 10204, DIN EN 12266 P10, P11, P12	88337125
3.1 Layer thickness measurement		88460229
3.1 Surface roughness measurement (only disc code B)		88094384

GEMÜ CONEXO

The interaction between valve components equipped with RFID chips and the corresponding IT infrastructure actively increases process reliability.



Thanks to serialization, every valve and every relevant valve component, such as the body, actuator, diaphragm or even automation components, can be clearly traced and read at any time using the RFID reader – the CONEXO pen. The CONEXO app, which can be installed on mobile devices, not only facilitates and improves the "installation qualification" process, but also makes the servicing process much more transparent and easier to document. The app actively guides the maintenance technician through the maintenance schedule and directly provides him with all the information assigned to the valve, such as test reports, testing documentation and maintenance histories. The CONEXO portal acts as a central element, helping to collect, manage and process all data.

For further information on GEMÜ CONEXO please visit:

www.gemu-group.com/conexo



GEMÜ Gebr. Müller Apparatebau GmbH & Co. KG
Fritz-Müller-Straße 6-8, 74653 Ingelfingen-Criesbach, Germany
Tel. +49 (0)7940 123-0 · info@gemue.de
www.gemu-group.com